

Garant
GARANT Master Mute boring bar, left-hand, Shank \varnothing / insert size: 20/11 mm

Order data

| | |
|--------------|---------------|
| Order number | 260921 20/11 |
| GTIN | 4067263623458 |
| Item class | 29E |

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

| | |
|--|----------------|
| Pack of insert screws | 269028 47 |
| Insert size | 11 mm |
| Overhang L_1 | 100 mm |
| Centre offset L_3 | 13 mm |
| suitable indexable insert | TC.. 1102.. |
| Minimum pre-drill $\varnothing D_{\min}$ | 25 mm |
| Setting angle κ | 90 degrees |
| Overall length L | 177 mm |
| Shank $\varnothing D_s$ | 20 mm |
| ISO code toolholder | A20X STFCL/L11 |
| Series | Master Mute |
| non-clamping range S | 120 mm |
| Standard | DIN 8024 |
| Application type | left-hand |

| | |
|-----------------|-------------------------------|
| Vibration | damped |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring bar |