

Garant
GARANT Master Mute boring bar, left-hand, Shank \varnothing / insert size: 16/06mm

Order data

Order number	260045 16/06
GTIN	4067263623380
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Overall length L	151 mm
Series	Master Mute
Centre offset L_3	11 mm
Overhang L_1	80 mm
Setting angle κ	95 degrees
ISO code toolholder	A16X SCLCR/L06
suitable indexable insert	CC.. 0602..
Shank $\varnothing D_s$	16 mm
Insert size	6 mm
Pack of insert screws	269028 38
Minimum pre-drill $\varnothing D_{min}$	20 mm
non-clamping range S	96 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar