

Garant**GARANT Master Mute boring bar, left-hand, Shank \varnothing / insert size: 32/09mm****Order data**

Order number	260045 32/09
GTIN	4067263623410
Item class	29E

Description**Version:**

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Overhang L_1	160 mm
Shank $\varnothing D_s$	32 mm
Insert size	9 mm
suitable indexable insert	CC.. 09T3..
Overall length L	277 mm
Series	Master Mute
Setting angle κ	95 degrees
Pack of insert screws	269028 50
ISO code toolholder	A30X SCLCR/L09
Centre offset L_3	22 mm
Minimum pre-drill $\varnothing D_{min}$	40 mm
non-clamping range S	192 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar