



## Base body Parallel shank, with through-coolant, 3×D, Type: 13



### Order data

Order number	232245 13
GTIN	4045197658074
Item class	22G

### Description

#### Version:

With internal cooling.

#### Straight fluted.

#### Note:

Further sizes available on request.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range  $D_c$ : 13 - 17.5 mm

Reach  $L_1$ : 34.9 mm

Shank  $\varnothing D_s$ : 20 mm

Shank length  $L_s$ : 50 mm

Clamping screws: 232990 TX8

### Technical description

Shank $\varnothing D_s$	20 mm
Clamping screws	232990 TX8
Dia. range $D_c$	13 - 17.5 mm
Reach $L_1$	34.9 mm
Shank length $L_s$	50 mm
Number of cutting edges Z	2
Version	3×D
Shank	ISO 9766

Through-coolant	yes
Type of product	Indexable drill

---

## Accessories

PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8
Torx® set of screws 10 pieces Drive TX8	232990 TX8
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3