



## PU coiled hose 1/2 inch with eSafe steel safety coupling Ø 11 × 16 mm, usable hose length: 4m



### Order data

Order number	080241 4
GTIN	7391390097477
Item class	08A

### Description

#### Version:

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant from -20 / 60 °C.

#### Supplied with:

Includes quick-release **safety** coupling No. 080285 and steel coupling adaptor No. 080290.

### Technical description

Material	PU spiral hose
Hose internal Ø	11 mm
Hose external Ø	16 mm
Colour	blue
Connection quick-release coupling	1/2 in
usable hose length	4 m

Connection plug nipple	1/2 in
maximum operating pressure	10 bar
maximum bursting pressure	35 bar
Type of product	Hose

---

## Accessories

Safety shut-offExternal thread Connection external thread 1/2 in	080285 1/2
Coupling adaptor with external thread5-piece set Connection external thread 1/2 in	080290 1/2