


BDMT 070304 ER-JS, PR1535, Type: INOX

Order data

Order number	227149 INOX
GTIN	4960664731169
Item class	25A

Description
Note:

Standard application values for $a_e = 0.3 \times D$. Exactly 90° up to $a_p = 4$ mm.

Technical description

Feed f_z per tooth	0.05 – 0.08 mm
Corner radius	0.4 mm
Type	INOX
Grade	PR1535
ISO code indexable insert	BDMT 070304 ER-JS
Grade	PR1535
Tool material	Carbide
Coating	coated
Type of product	Indexable insert for milling

User data

	Suitability	V_c	ISO code
INOX < 900 N/mm ²	suitable	160 m/min	M
INOX > 900 N/mm ²	suitable	160 m/min	M
Ti > 850 N/mm ²	suitable	50 m/min	S
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		