

Mitutoyo**Digital height gauge and marking-out system with data output, Marking height: 600mm****Order data**

Order number	445136 600
GTIN	4946368859255
Item class	44A

Description**Version:**

ABSOLUTE scale, no new reference point setting after switching on again and unlimited travel speed. Large and smooth-running handwheel. Carbide-tipped scriber and Digimatic data output. Large LCD display (digit height 12 mm) for easy, error-free reading.

Supplied with:

Including battery No. 081560 size 357, 1 carbide-tipped scriber No. 443510 size 300.

Optional extras:

Holder No. 445180, data cable No. 497080.

Technical description

Battery life approx.	20000 h
Error limit	0.05 mm
Column cross section	35×12 mm
Scale divisions	0.01 mm
Number of batteries contained	1

Marking height	600 mm
Base width	120 mm
Power supply	Battery-powered
Base length	180 mm
Article no of the battery / rechargeable battery fitted	081560 357
Standard	Works standard
Height of numerals	12 mm
Interface	USB interface
Interface	USB interface
Measured value saving	Once-off setting of the zero position
Preset function	yes
Measurement technology	digital
Calibration	E1
Type of product	Height gauge and marking device

Services

CalibrationHeight gauge / height scriber maximum measuring range 1000 mm	024630 1000
DAkkS calibrationHeight gauge / height scriber maximum measuring range 1000 mm	024640 1000

Accessories

Button cell / special battery Battery type 357	081560 357
Spare scriber, carbide tipped for marking heights 300 mm	443510 300