



Base body MT shank, without through-coolant, 8×D, Type: 36



Order data

Order number	232265 36
GTIN	4045197592651
Item class	22G

Description

Version:

For holes up to IT10 accuracy. **Straight fluted.**

Note:

Further sizes available on request.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530.**

Reduce feed rates f by 5% and v_c values by 10%.

Technical description

Reach L_1	349.3 mm
Clamping screws	232990 TX20
Dia. range D_c	36 - 47 mm
Morse taper MT size	4
Number of cutting edges Z	2
Version	8×D
Shank	Morse taper
Through-coolant	no
Type of product	Indexable drill

Accessories

Torx® set of screws 10 pieces Drive TX15	232990 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torx® set of screws 10 pieces Drive TX20	232990 TX20
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600