



## Base body MT shank, without through-coolant, 5×D, Type: 13



### Order data

Order number	232260 13
GTIN	4045197592569
Item class	22G

### Description

#### Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Through-coolant: no

Number of cutting edges Z: 2

Dia. range  $D_c$ : 13 - 17.5 mm

Reach  $L_1$ : 63.5 mm

Morse taper MT size: 2

Clamping screws: 232990 TX8

### Technical description

Reach $L_1$	63.5 mm
Clamping screws	232990 TX8
Dia. range $D_c$	13 - 17.5 mm
Morse taper MT size	2
Number of cutting edges Z	2
Version	5×D
Shank	Morse taper
Through-coolant	no
Type of product	Indexable drill

---

## Accessories

PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8
Torx® set of screws 10 pieces Drive TX8	232990 TX8
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3