



Base body MT shank, without through-coolant, 8×D, Type: 48



Order data

Order number	232265 48
GTIN	4045197592668
Item class	22G

Description

Version:

For holes up to IT10 accuracy. **Straight fluted.**

Note:

Further sizes available on request.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Reduce feed rates f by 5% and v_c values by 10%.

Technical description

Clamping screws	232990 TX20
Dia. range D_c	48 - 65 mm
Reach L_1	422.3 mm
Morse taper MT size	5
Number of cutting edges Z	2
Version	8×D
Shank	Morse taper
Through-coolant	no
Type of product	Indexable drill

Accessories

8 mm blade with magnetwith 1/4 inch bit holder overall length 50 mm	659874 50
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Torx® set of screws10 pieces Drive TX20	232990 TX20
Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600