

**Garant**
**GARANT Master Mute boring bar, right-hand, Shank  $\varnothing$  / insert size: 16/11mm**

**Order data**

Order number	260920 16/11
GTIN	4067263623137
Item class	29E

**Description**
**Version:**

Round shank without clamping face.

**Note:**

Do not clamp on the area marked S!

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	20 mm
Overhang $L_1$	80 mm
suitable indexable insert	TC.. 1102..
Centre offset $L_3$	11 mm
Insert size	11 mm
Overall length L	150 mm
ISO code toolholder	A16X STFCCR/L11
Series	Master Mute
Shank $\varnothing D_s$	16 mm
Pack of insert screws	269028 38
Setting angle $\kappa$	90 degrees
non-clamping range S	96 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar