

Garant
GARANT Master Mute boring bar, left-hand, Shank \varnothing / insert size: 16/11 mm

Order data

Order number	260921 16/11
GTIN	4067263623441
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Insert size	11 mm
Pack of insert screws	269028 38
Shank $\varnothing D_s$	16 mm
Overhang L_1	80 mm
Centre offset L_3	11 mm
Overall length L	150 mm
suitable indexable insert	TC.. 1102..
Minimum pre-drill $\varnothing D_{min}$	20 mm
Setting angle κ	90 degrees
Series	Master Mute
ISO code toolholder	A16X STFCL/L11
non-clamping range S	96 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar