

Garant
GARANT Master Mute boring bar, left-hand, Shank \varnothing / insert size: 12/11 mm

Order data

Order number	260921 12/11
GTIN	4067263623434
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Insert size	11 mm
Series	Master Mute
Pack of insert screws	269028 38
suitable indexable insert	TC.. 1102..
Minimum pre-drill $\varnothing D_{\min}$	16 mm
Setting angle κ	90 degrees
Overhang L_1	60 mm
Shank $\varnothing D_s$	12 mm
Centre offset L_3	9 mm
Overall length L	120 mm
ISO code toolholder	A12X STFCL/L11
non-clamping range S	72 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar