



Base body Parallel shank, with through-coolant, 5×D, Type: 12



Order data

Order number	232250 12
GTIN	4045197589033
Item class	22G

Description

Version:

With internal cooling.

Note:

Further sizes available on request.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range D_c : 12 - 12.5 mm

Reach L_1 : 60.3 mm

Shank $\varnothing D_s$: 20 mm

Shank length L_s : 50 mm

Clamping screws: 232990 TX7

Technical description

Dia. range D_c	12 - 12.5 mm
Clamping screws	232990 TX7
Shank $\varnothing D_s$	20 mm
Reach L_1	60.3 mm
Shank length L_s	50 mm
Number of cutting edges Z	2
Version	5×D
Shank	ISO 9766
Through-coolant	yes

Type of product

Indexable drill

Accessories

Torque screwdriver, fixed setting set torque 0,6 N·m

211750 0,6

Torx® set of screws 10 pieces Drive TX7

232990 TX7

PrecisionBit for Torx®, shank E 6.3 Torx® profile TX7

674248 TX7