

Garant**Digital external micrometer set HCT IP67 and Bluetooth, Measuring range: 0-100mm****Order data**

Order number	421577 0-100
GTIN	4067263036692
Item class	41B

Description**Version:**

Innovative external micrometer IP67 HCT with Bluetooth 5.0 and **12 mm digits** on a high-contrast display. Very long battery running time due to modern energy-efficient measurement system. Due to the automatic shut-off feature, very long battery runtimes are achieved. Practical HOLD function for freezing the measured value for reliable, error-free reading. Measuring spindle hardened and ground. Carbide anvils. High performance ratchet with quick operation. Painted steel frame with thermal insulation. Button for changeover between relative and absolute measurement. Zero setting in any position.

Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app (available free of charge for Android and iOS) and the HCT Windows app (available for Windows). Can also be used via a Human Interface Device (HID).

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

External micrometer No. 421575. Setting standards.

Technical description

Number of micrometers	4
-----------------------	---

Series	HCT
Wireless application	HID (Human Interface Device)
Wireless application	HCT Mobile App
Wireless application	HCT Windows app
Battery type	Button cell
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of micrometer standards	3
Number of batteries contained	4
IP Index of Protection	IP 67
Power supply	Battery-powered
Measuring range	0 - 100 mm
Standard	Works standard
Reversible reading	mm / inch
Interface	Bluetooth interface
Measurement technology	digital
Packaging	sturdy box
Calibration	S2
Type of product	External tube micrometer

Services

Calibration External micrometer set Measuring range 0-100 mm	020430 0-100
DAkkS calibration External micrometer set Measuring range 0-100 mm	020440 0-100

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------