



LED floodlight CONNECT, Type: VEGA-4



Order data

Order number	081236 VEGA-4
GTIN	5708997006764
Item class	07A

Description

Version:

Scangrip CONNECT work lamps are based on the CAS system and are also compatible with 18-V batteries from all leading power tool manufacturers.

High-performance cordless LED floodlight with uniform, non-dazzle illumination. The sturdy, shock-resistant plastic housing of the lamps is perfect for all working environments. Can be mounted on the SCANGRIP® stand. For CAS 18-V batteries, 18-V batteries from leading power tool manufacturers or direct connection to the SCANGRIP® power supply.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Lamps are supplied without battery and charger.

Note:

Suitable batteries, chargers and power supply units for wired power supply can be found under 073870 – 073890 and 081249.

Technical description

Overall width	103 mm
Overall length	280 mm
Illumination	4000 lm

Power supply	Mains operated
Battery voltage	18 V
Number of rechargeable batteries contained	0
IP Index of Protection	IP 54
Overall height	288 mm
Type of rechargeable battery	Lithium-ion
Type of product	Area light