

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 8/06mm


Order data

Order number	269984 8/06
GTIN	4067263786818
Item class	21T

Technical description

Centre offset L_3	5 mm
Insert size	6 mm
ISO code toolholder	A08H SCLCR/L06
Clamping height L_2	7 mm
Minimum pre-drill $\varnothing D_{\min}$	10 mm
Overall length L	100 mm
suitable indexable insert	CC.. 0602..
Head length L_1	20 mm
Shank $\varnothing D_s$	8 mm
Pack of insert screws	269028 7
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

