

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 10/06mm


Order data

Order number	269984 10/06
GTIN	4067263786825
Item class	21T

Technical description

Insert size	6 mm
Clamping height L_2	9 mm
Shank $\varnothing D_s$	10 mm
Minimum pre-drill $\varnothing D_{min}$	12 mm
Overall length L	125 mm
Pack of insert screws	269028 7
Centre offset L_3	6 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	A10K SCLCR/L06
Head length L_1	20 mm
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

