

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 20/09mm

Order data

Order number	269984 20/09
GTIN	4067263786856
Item class	21T

Technical description

Clamping height L_2	18 mm
Overall length L	200 mm
Pack of insert screws	269028 8
Insert size	9 mm
Centre offset L_3	11 mm
Head length L_1	36 mm
ISO code toolholder	A20R SCLCR/L09
Shank $\varnothing D_s$	20 mm
suitable indexable insert	CC.. 09T3..
Minimum pre-drill $\varnothing D_{min}$	22 mm
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

