

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 12/06mm**

**Order data**

Order number	269984 12/06
GTIN	4067263786832
Item class	21T

**Technical description**

Centre offset $L_3$	7 mm
ISO code toolholder	A12L SCLCR/L06
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Clamping height $L_2$	11 mm
Overall length $L$	140 mm
Pack of insert screws	269028 7
Head length $L_1$	24.3 mm
Shank $\varnothing D_s$	12 mm
Insert size	6 mm
suitable indexable insert	CC.. 0602..
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

