

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 25/09mm**


## Order data

Order number	269984 25/09
GTIN	4067263786863
Item class	21T

## Technical description

Overall length L	200 mm
Head length L <sub>1</sub>	43 mm
Minimum pre-drill $\varnothing D_{\min}$	27 mm
Insert size	9 mm
Centre offset L <sub>3</sub>	13.5 mm
Clamping height L <sub>2</sub>	23 mm
suitable indexable insert	CC.. 09T3..
ISO code toolholder	A25R SCLCR/L09
Shank $\varnothing D_s$	25 mm
Pack of insert screws	269028 8
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

