

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 25/12mm

Order data

Order number	269984 25/12
GTIN	4067263786870
Item class	21T

Technical description

ISO code toolholder	A25R SCLCR/L12
Insert size	12 mm
Head length L_1	43 mm
Centre offset L_3	13.5 mm
suitable indexable insert	CC.. 1204..
Shank $\varnothing D_s$	25 mm
Clamping height L_2	23 mm
Overall length L	200 mm
Minimum pre-drill $\varnothing D_{min}$	27 mm
Pack of insert screws	269028 9
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

