

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 16/09mm


Order data

Order number	269985 16/09
GTIN	4067263786917
Item class	21T

Technical description

Overall length L	180 mm
Pack of insert screws	269028 8
ISO code toolholder	A16Q SCLCR/L09
Centre offset L ₃	9 mm
Head length L ₁	31 mm
Minimum pre-drill Ø D _{min}	18 mm
Shank Ø D _s	16 mm
Clamping height L ₂	15 mm
suitable indexable insert	CC.. 09T3..
Insert size	9 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

