

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 25/09mm

Order data

Order number	269985 25/09
GTIN	4067263786931
Item class	21T

Technical description

suitable indexable insert	CC.. 09T3..
Insert size	9 mm
Head length L ₁	43 mm
Overall length L	200 mm
ISO code toolholder	A25R SCLCR/L09
Clamping height L ₂	23 mm
Minimum pre-drill Ø D _{min}	27 mm
Pack of insert screws	269028 8
Centre offset L ₃	13.5 mm
Shank Ø D _s	25 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

