

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 10/06mm

Order data

Order number	269985 10/06
GTIN	4067263786894
Item class	21T

Technical description

Shank Ø D _s	10 mm
Pack of insert screws	269028 7
suitable indexable insert	CC.. 0602..
Centre offset L ₃	6 mm
Minimum pre-drill Ø D _{min}	12 mm
Overall length L	125 mm
Clamping height L ₂	9 mm
Head length L ₁	20 mm
Insert size	6 mm
ISO code toolholder	A10K SCLCR/L06
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

