

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 20/09mm**

**Order data**

Order number	269985 20/09
GTIN	4067263786924
Item class	21T

**Technical description**

Centre offset $L_3$	11 mm
Clamping height $L_2$	18 mm
Overall length $L$	200 mm
suitable indexable insert	CC.. 09T3..
ISO code toolholder	A20R SCLCR/L09
Shank Ø $D_s$	20 mm
Minimum pre-drill Ø $D_{min}$	22 mm
Head length $L_1$	36 mm
Pack of insert screws	269028 8
Insert size	9 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

