

**Garant**
**Boring bar, steel, left-hand, Shank  $\varnothing$  / insert size: 8/06mm**

**Order data**

Order number	269985 8/06
GTIN	4067263786887
Item class	21T

**Technical description**

Shank $\varnothing$ $D_s$	8 mm
Centre offset $L_3$	5 mm
Head length $L_1$	20 mm
Minimum pre-drill $\varnothing$ $D_{min}$	10 mm
Clamping height $L_2$	7 mm
Pack of insert screws	269028 7
Insert size	6 mm
Overall length $L$	100 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	A08H SCLCR/L06
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

