

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 12/06mm

Order data

Order number	269985 12/06
GTIN	4067263786900
Item class	21T

Technical description

Pack of insert screws	269028 7
Insert size	6 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	A12L SCLCR/L06
Clamping height L_2	11 mm
Shank Ø D_s	12 mm
Minimum pre-drill Ø D_{min}	14 mm
Centre offset L_3	7 mm
Overall length L	140 mm
Head length L_1	24.3 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

