

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 12/07mm**


## Order data

Order number	269986 12/07
GTIN	4067263786962
Item class	21T

## Technical description

ISO code toolholder	A12L SDUCR/L07
Centre offset $L_3$	8 mm
Clamping height $L_2$	11 mm
Insert size	7 mm
Shank $\varnothing D_s$	12 mm
Pack of insert screws	269028 7
Head length $L_1$	25 mm
suitable indexable insert	DC.. 0702..
Overall length L	140 mm
Minimum pre-drill $\varnothing D_{min}$	15 mm
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

