

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 20/11mm**


## Order data

Order number	269986 20/11
GTIN	4067263786993
Item class	21T

## Technical description

Head length $L_1$	36 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Centre offset $L_3$	13 mm
Insert size	11 mm
ISO code toolholder	A20R SDUCR/L11
Shank $\varnothing D_s$	20 mm
Overall length $L$	200 mm
Clamping height $L_2$	18 mm
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

