

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 25/11 mm

Order data

Order number	269986 25/11
GTIN	4067263787006
Item class	21T

Technical description

Centre offset L_3	16 mm
Head length L_1	40 mm
Clamping height L_2	23 mm
Insert size	11 mm
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
ISO code toolholder	A25R SDUCR/L11
Overall length L	200 mm
Minimum pre-drill $\varnothing D_{\min}$	31 mm
Shank $\varnothing D_s$	25 mm
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

