

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 25/12mm**

**Order data**

Order number	269985 25/12
GTIN	4067263786948
Item class	21T

**Technical description**

Insert size	12 mm
Clamping height $L_2$	23 mm
Overall length $L$	200 mm
Shank Ø $D_s$	25 mm
Minimum pre-drill Ø $D_{min}$	27 mm
suitable indexable insert	CC.. 1204..
Head length $L_1$	43 mm
ISO code toolholder	A25R SCLCR/L12
Pack of insert screws	269028 9
Centre offset $L_3$	13.5 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

