

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 16/07mm**

**Order data**

Order number	269986 16/07
GTIN	4067263786979
Item class	21T

**Technical description**

Insert size	7 mm
Shank $\varnothing$ D <sub>s</sub>	16 mm
Centre offset L <sub>3</sub>	10 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing$ D <sub>min</sub>	19 mm
Head length L <sub>1</sub>	28 mm
ISO code toolholder	A16Q SDUCR/L07
suitable indexable insert	DC.. 0702..
Clamping height L <sub>2</sub>	15 mm
Overall length L	180 mm
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

