

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 10/07mm

Order data

Order number	269987 10/07
GTIN	4067263787013
Item class	21T

Technical description

ISO code toolholder	A10K SDUCR/L07
Centre offset L_3	7 mm
Overall length L	125 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
suitable indexable insert	DC.. 0702..
Head length L_1	20 mm
Pack of insert screws	269028 7
Clamping height L_2	9 mm
Insert size	7 mm
Shank $\varnothing D_s$	10 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

