

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 10/07mm**

**Order data**

Order number	269986 10/07
GTIN	4067263786955
Item class	21T

**Technical description**

Pack of insert screws	269028 7
Head length $L_1$	20 mm
Insert size	7 mm
Centre offset $L_3$	7 mm
Overall length $L$	125 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	A10K SDUCR/L07
Shank $\varnothing D_s$	10 mm
Minimum pre-drill $\varnothing D_{min}$	13 mm
Clamping height $L_2$	9 mm
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

