

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 16/11mm


Order data

Order number	269986 16/11
GTIN	4067263786986
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	23 mm
suitable indexable insert	DC.. 11T3..
Centre offset L_3	14 mm
Shank $\varnothing D_s$	16 mm
Head length L_1	28 mm
ISO code toolholder	A16Q SDUCR/L11
Insert size	11 mm
Clamping height L_2	15 mm
Pack of insert screws	269028 8
Overall length L	180 mm
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

