

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 12/07mm**


## Order data

Order number	269987 12/07
GTIN	4067263787020
Item class	21T

## Technical description

ISO code toolholder	A12L SDUCR/L07
Overall length L	140 mm
Pack of insert screws	269028 7
Head length L <sub>1</sub>	25 mm
Clamping height L <sub>2</sub>	11 mm
Centre offset L <sub>3</sub>	8 mm
suitable indexable insert	DC.. 0702..
Minimum pre-drill Ø D <sub>min</sub>	15 mm
Shank Ø D <sub>s</sub>	12 mm
Insert size	7 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

