

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 16/07mm

Order data

Order number	269987 16/07
GTIN	4067263787037
Item class	21T

Technical description

Head length L ₁	28 mm
Overall length L	180 mm
Centre offset L ₃	10 mm
ISO code toolholder	A16Q SDUCR/L07
Clamping height L ₂	15 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
Minimum pre-drill Ø D _{min}	19 mm
Insert size	7 mm
Shank Ø D _s	16 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

