

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 16/11 mm

Order data

Order number	269987 16/11
GTIN	4067263787044
Item class	21T

Technical description

Overall length L	180 mm
suitable indexable insert	DC.. 11T3..
Pack of insert screws	269028 8
ISO code toolholder	A16Q SDUCR/L11
Head length L ₁	28 mm
Clamping height L ₂	15 mm
Centre offset L ₃	14 mm
Minimum pre-drill Ø D _{min}	23 mm
Shank Ø D _s	16 mm
Insert size	11 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

