

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 20/11 mm

Order data

Order number	269987 20/11
GTIN	4067263787051
Item class	21T

Technical description

Head length L_1	36 mm
Clamping height L_2	18 mm
Centre offset L_3	13 mm
Overall length L	200 mm
Pack of insert screws	269028 8
ISO code toolholder	A20R SDUCR/L11
suitable indexable insert	DC.. 11T3..
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Insert size	11 mm
Shank $\varnothing D_s$	20 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

