

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 25/11 mm

Order data

Order number	269987 25/11
GTIN	4067263787068
Item class	21T

Technical description

Overall length L	200 mm
Pack of insert screws	269028 8
Minimum pre-drill Ø D _{min}	31 mm
Clamping height L ₂	23 mm
Centre offset L ₃	16 mm
suitable indexable insert	DC.. 11T3..
Head length L ₁	40 mm
ISO code toolholder	A25R SDUCR/L11
Shank Ø D _s	25 mm
Insert size	11 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

