

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 10/07mm**

**Order data**

Order number	269988 10/07
GTIN	4067263787075
Item class	21T

**Technical description**

suitable indexable insert	DC.. 0702..
Overall length L	125 mm
Clamping height L <sub>2</sub>	9 mm
ISO code toolholder	A10K SDQCR/L07
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Shank $\varnothing D_s$	10 mm
Head length L <sub>1</sub>	20 mm
Centre offset L <sub>3</sub>	7 mm
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar