

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	269988 12/07
GTIN	4067263787082
Item class	21T

Technical description

Clamping height L_2	11 mm
Pack of insert screws	269028 7
Shank $\varnothing D_s$	12 mm
Overall length L	140 mm
ISO code toolholder	A12L SDQCR/L07
Centre offset L_3	8 mm
Head length L_1	25 mm
Minimum pre-drill $\varnothing D_{min}$	15 mm
suitable indexable insert	DC.. 0702..
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar