

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 10/07mm**

**Order data**

Order number	269989 10/07
GTIN	4067263787136
Item class	21T

**Technical description**

ISO code toolholder	A10K SDQCR/L07
Centre offset $L_3$	7 mm
Clamping height $L_2$	9 mm
suitable indexable insert	DC.. 0702..
Head length $L_1$	20 mm
Pack of insert screws	269028 7
Overall length L	125 mm
Shank Ø $D_s$	10 mm
Minimum pre-drill Ø $D_{min}$	13 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar