

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 16/07mm

Order data

Order number	269988 16/07
GTIN	4067263787099
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	19 mm
Head length L_1	28 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Clamping height L_2	15 mm
ISO code toolholder	A16Q SDQCR/L07
Overall length L	180 mm
Shank $\varnothing D_s$	16 mm
Centre offset L_3	10 mm
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar