

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 20/11 mm

Order data

Order number	269989 20/11
GTIN	4067263787174
Item class	21T

Technical description

ISO code toolholder	A20R SDQCR/L11
Shank Ø D _s	20 mm
Clamping height L ₂	18 mm
Head length L ₁	36 mm
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Overall length L	200 mm
Minimum pre-drill Ø D _{min}	25 mm
Centre offset L ₃	13 mm
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar