

Garant
Boring bar, steel, left-hand, Shank Ø / insert size: 16/07mm


Order data

Order number	269989 16/07
GTIN	4067263787150
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	19 mm
Pack of insert screws	269028 7
Clamping height L_2	15 mm
Head length L_1	28 mm
ISO code toolholder	A16Q SDQCR/L07
Shank Ø D_s	16 mm
Centre offset L_3	10 mm
Overall length L	180 mm
suitable indexable insert	DC.. 0702..
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar