

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	269988 20/11
GTIN	4067263787112
Item class	21T

Technical description

ISO code toolholder	A20R SDQCR/L11
Overall length L	200 mm
Head length L ₁	36 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	DC.. 11T3..
Shank $\varnothing D_s$	20 mm
Pack of insert screws	269028 8
Centre offset L ₃	13 mm
Clamping height L ₂	18 mm
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar