

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 25/11 mm**

**Order data**

Order number	269988 25/11
GTIN	4067263787129
Item class	21T

**Technical description**

Clamping height $L_2$	23 mm
Overall length $L$	200 mm
Minimum pre-drill $\varnothing D_{\min}$	31 mm
suitable indexable insert	DC.. 11T3..
ISO code toolholder	A25R SDQCR/L11
Centre offset $L_3$	16 mm
Head length $L_1$	40 mm
Pack of insert screws	269028 8
Shank $\varnothing D_s$	25 mm
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar