

**Garant**
**Boring bar, steel, left-hand, Shank Ø / insert size: 16/11 mm**

**Order data**

Order number	269989 16/11
GTIN	4067263787167
Item class	21T

**Technical description**

Centre offset $L_3$	14 mm
suitable indexable insert	DC.. 11T3..
Minimum pre-drill $\varnothing D_{\min}$	23 mm
Head length $L_1$	28 mm
Overall length $L$	180 mm
Shank $\varnothing D_s$	16 mm
Pack of insert screws	269028 8
Clamping height $L_2$	15 mm
ISO code toolholder	A16Q SDQCR/L11
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar